


2D Video APP: Starterstkit  
Quick Start



1. **Install Light Meter App on your mobile phone**
  - a. Controle light: 800lx is needed for high Speed

2. **Position camera to subject on treadmill** (Type IDS UI-3240LE-C-HQ)



Hight: camera to ground  
60 cm


Wide: camera to subject  
160 cm

3. **Position Camera on the Tripod** (Type IDS UI-3240LE-C-HQ)



The camera is turned 90° on the Tripod

This is an opportunity to use maximum resolution of a walking (running) subject



**Focus of the lens** (type Kowa LMVZ4411)

